



TYA624A



Shutter module 4x 6A /230V~, KNX

Technical Features

Settings

Supported configuration mode	ETS
------------------------------	-----

Connectivity

With bus system KNX radio	No
---------------------------	----

Installation, mounting

Mounting on	DIN rail
-------------	----------

Materials

Colour	Light grey
--------	------------

Equipment

With switch for manual switch	Yes
-------------------------------	-----

Electric current

Rated current	6 A
Max. switching current	6 A

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Capacity

Number of modules	4
-------------------	---

Texts

Function	With positioning function for roller shutter position With safety functions e.g. for wind, rain, alarm With sun shade function
Type of connection	With quickconnect plug-in terminals
Operating mode	Operating mode only roller shutters

Sustainability

RoHS conform	Yes
--------------	-----