



TYA624C



Output device for 4 shutters or blinds 230V~

Technical Features

Settings

Supported configuration mode ETS

Connectivity

With bus system KNX radio No

Installation, mounting

Mounting on DIN rail

Materials

Colour Light grey

Equipment

With switch for manual switch Yes

Electric current

Rated current 6 A

Max. switching current 6 A

Voltage

Operating voltage over bus 21 - 32 V

Use conditions

Operating temperature -5 - 45 °C

Connection

Cross-section flexible conductor 0.75 - 2.5 mm²

Cross-section rigid conductor 0.75 - 2.5 mm²

Capacity

Number of modules 4

Texts

Function With safety functions e.g. for wind, rain, alarm
With positioning function for blind and lamella position
With sun shade function

Type of connection With quickconnect plug-in terminals

Operating mode Operating mode can be set for roller shutter/awning

Sustainability

RoHS conform Yes