



WBWP2S

**Socket IP53 twin horizontal 10A**

**Technical Features**

**Electric current**

Rated current	10 A
---------------	------

**Voltage**

Nominal voltage	250 - 250 V
-----------------	-------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	Light grey
Surface finish	Glossy
Material	Glass Thermoplastic
Treatment	Untreated

**Dimensions**

Height	85 mm
Width	115 mm
Depth	88 mm

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	2
-------------------	---

**Safety**

Impact resistance IK	IK08
Ingress Protection (IP) class	IP53

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	Without imprint
Cover	Complete housing
Protection	Without enhanced contact protection
Type of connection	With screw terminals

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes