



WBWP1S

Socket IP53 single horizontal 10A

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Light grey
Surface finish	Glossy
Material	Glass Thermoplastic
Treatment	Untreated

Dimensions

Height	85 mm
Width	85 mm
Depth	88 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP53

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Complete housing
Protection	Without enhanced contact protection
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes