



WBWP1S

Socket IP53 single horizontal 10A

Technical Features

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Light grey
Surface finish	Glossy
Material	Glass Thermoplastic
Treatment	Untreated

Dimensions

Height	85 mm
Width	85 mm
Depth	88 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP53

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
Protection	Without enhanced contact protection
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes