Product Datasheet
SK602

SK602

Voltmeter switch 3"o

Technical Features

Electric current	
Rated current	20 A
Capacity	
Number of modules	3
Frequency	
Frequency	50 - 50 Hz
Use conditions	
Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C
Connectivity	
Type of connection	Screw terminal
Connection	
Cross-section flexible conductor	1.5 - 10 mm^2
Cross-section rigid conductor	1 - 6 mm^2
Power	
Total power loss under IN	1 W
Dimensions	
Height	85 mm
Width	70 mm
Depth	64 mm
Safety	
Ingress Protection (IP) class	IP20
Installation, mounting	
Mounting on	DIN rail
Voltage	
Rated insulation voltage Ui	690 V
Sustainability	
Halogen free	Yes
REACh-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings