



SK603

Ammeter switch 3 O

Technical Features

Electric current

Rated current	20 A
---------------	------

Capacity

Number of modules	3
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1.5 - 10 mm ²
Cross-section rigid conductor	1 - 6 mm ²

Power

Total power loss under IN	1 W
---------------------------	-----

Dimensions

Height	85 mm
Width	70 mm
Depth	64 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Voltage

Rated insulation voltage Ui	690 V
Rated operational voltage Ue	400 - 400 V

Installation, mounting

Mounting on	DIN rail
-------------	----------

Architecture

Type of pole	3P+N
--------------	------

Equipment

With battery	No
--------------	----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

