



SK603

**Ammeter switch 3 O**

**Technical Features**

**Electric current**

Rated current 20 A

**Capacity**

Number of modules 3

**Frequency**

Frequency 50 - 50 Hz

**Use conditions**

Operating temperature -10 - 40 °C

Storage/transport temperature -40 - 80 °C

**Connectivity**

Type of connection Screw terminal

**Connection**

Cross-section flexible conductor 1.5 - 10 mm<sup>2</sup>

Cross-section rigid conductor 1 - 6 mm<sup>2</sup>

**Power**

Total power loss under IN 1 W

**Dimensions**

Height 85 mm

Width 70 mm

Depth 64 mm

**Safety**

Ingress Protection (IP) class IP20

**Voltage**

Rated insulation voltage U<sub>i</sub> 690 V

Rated operational voltage U<sub>e</sub> 400 - 400 V

**Installation, mounting**

Mounting on DIN rail

**Architecture**

Type of pole 3P+N

**Equipment**

With battery No

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes

Illustrations | Drawings

