



SK603

## Ammeter switch 3 O

### Technical Features

#### Electric current

Rated current	20 A
---------------	------

#### Capacity

Number of modules	3
-------------------	---

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Use conditions

Operating temperature	-10 - 40 °C
-----------------------	-------------

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Connection

Cross-section flexible conductor	1.5 - 10 mm <sup>2</sup>
----------------------------------	--------------------------

Cross-section rigid conductor	1 - 6 mm <sup>2</sup>
-------------------------------	-----------------------

#### Power

Total power loss under IN	1 W
---------------------------	-----

#### Dimensions

Height	85 mm
--------	-------

Width	70 mm
-------	-------

Depth	64 mm
-------	-------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Voltage

Rated insulation voltage Ui	690 V
-----------------------------	-------

Rated operational voltage Ue	400 - 400 V
------------------------------	-------------

#### Installation, mounting

Mounting on	DIN rail
-------------	----------

#### Architecture

Type of pole	3P+N
--------------	------

#### Equipment

With battery	No
--------------	----

#### Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

