



WMINDRED

Indicator Module RED

Technical Features

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Dimensions

Height 60 mm

Width 25 mm

Depth 24 mm

Connectivity

Mounting type Clamp mounting

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -15 - 40 °C

Texts

Imprint Without imprint

Sustainability

REACH-SVHC free Yes