



WMINDRED

**Indicator Module RED**

**Technical Features**

**Frequency**

Frequency 50 - 60 Hz

**Lighting**

Type of lamp LED

**Materials**

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

**Dimensions**

Height 60 mm

Width 25 mm

Depth 24 mm

**Connectivity**

Mounting type Clamp mounting

**Safety**

Ingress Protection (IP) class IP20

**Use conditions**

Operating temperature -15 - 40 °C

**Texts**

Imprint Without imprint

**Sustainability**

REACH-SVHC free Yes