



SK600

Selector switch non spring ret

Technical Features

Architecture

Number of poles	1
Type of pole	1P

Electric current

Rated current	20 A
Rated conditional short-circuit current I _{cc} with gl-gG fuses	8 kA

Voltage

Rated operational voltage U _e	660 - 660 V
Type voltage supply	AC
Rated insulation voltage U _i	690 V

Capacity

Number of modules	3
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Dimensions

Height	85 mm
Width	53 mm
Depth	64 mm
Dimensions	85 x 53 mm

Equipment

Number of NO contacts	0
Number of NC contacts	0

Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section flexible conductor	1.5 - 10 mm ²
Cross-section rigid conductor	1 - 6 mm ²

Power

Total power loss under I _N	0.70 W
---------------------------------------	--------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

