



HA407

Load break switch with visible breaking 4P 160A

Technical Features

Electric current

Rated current	160 A
Acceptable current rating AC21	160 A
Acceptable current rating AC21 category A	160 A
Acceptable current rating AC21 category B	160 A
Acceptable current rating AC22 category A	160 A
Acceptable current rating AC23 category A	160 A
Acceptable current rating AC23 category B	160 A
Rated short-circuit making capacity I _{cm} under 415 V AC according to IEC 60947-3	5.88 kA
Rated short-time withstand current I _{cw} 1s IEC 60947	4 kA
Rated short-time withstand current I _{cw} IEC 60947	4 kA

Architecture

Type of pole	4P
Number of poles	4

Connection

Cross-section rigid conductor	95 mm ²
Cross-section flexible conductor	95 mm ²

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V
Rated operational voltage U _e	380 - 415 V

Power

Power loss per pole at I _n	3.30 W
Total power loss under I _N	9.90 W
Rated operational power under 400 V AC AC1	105000 W
Rated operational power under 400 V AC AC23	72000 W

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Architecture

Control/operation element	Short rotary handle
---------------------------	---------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes

Installation, mounting

Nominal tightening torque	9 - 9.9 Nm
---------------------------	------------

Capacity

Number of modules	8.50
-------------------	------

Dimensions

Height	82.5 mm
Width	142 mm
Depth	136 mm

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

