



4538



FCC soc. out., 8-pole, cat.3, com-tech, white

Technical Features

Frequency

Transmission bandwidth 16 - 16 MHz

Equipment

Number of outputs 1

Materials

Colour White

Connection

Connector/plug type Screw terminal

Safety

Ingress Protection (IP) class IP20

Voltage

Rated voltage 125 V

Electric current

Rated current 1 A

Dimensions

Built-in depth 22 mm

Texts

Outlet With 45° oblique outlet

Installation mode With spreader claws

Category/ports Cat.3

Protection No

Type of connection With screw terminals

Sustainability

REACH-SVHC free Yes

RoHS conform Yes