



KDN363B



Insulated busbar 3P 63A fork 10mm² 57M

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 3

Dimensions

Length 1000 mm

Voltage

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 230 - 400 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 57

Sustainability

REACH-SVHC free Yes

RoHS conform Yes