



G4741

**Connection 3000mm, Schuko-angle-plug/socket**

**Technical Features**

**Architecture**

Number of poles	3
-----------------	---

**Voltage**

Max. operating voltage	250 V
Nominal voltage	230 - 230 V
Rated surge voltage	4 kV

**Electric current**

Rated current	16 A
---------------	------

**Cable**

Cable diameter	11 mm
----------------	-------

**Connection**

Conductor cross-section	1.50 - 1.50 mm <sup>2</sup>
Connector/plug type	Wago Winsta

**Cover, door**

Interlockable	No
---------------	----

**Connectivity**

Number of wires	3
-----------------	---

**Equipment**

Mechanical coding	Yes
Type cable side 1	Jack
Type cable side 2	Jack
Type of cable	Device connection cable

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

**Materials**

Colour	Black
Colour contact insert	Black

**Power**

Fire load	1.92 kWh
-----------	----------

**Resistance**

Continuity resistor	1 mΩ
---------------------	------

**Cable**

Cable permanent temperature resistant to	70 °C
--	-------

**Sustainability**

RoHS conform	Yes
--------------	-----