



G4761

Connection 5000mm, Schuko-angle-plug/socket

Technical Features

Architecture

Number of poles	3
-----------------	---

Voltage

Max. operating voltage	250 V
Nominal voltage	230 - 230 V
Rated surge voltage	4 kV

Electric current

Rated current	16 A
---------------	------

Cable

Cable diameter	11 mm
----------------	-------

Connection

Conductor cross-section	1.50 - 1.50 mm ²
Connector/plug type	Wago Winsta

Cover, door

Interlockable	No
---------------	----

Connectivity

Number of wires	3
-----------------	---

Equipment

Mechanical coding	Yes
Type cable side 1	Jack
Type cable side 2	Jack
Type of cable	Device connection cable

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Materials

Colour	Black
Colour contact insert	Black

Power

Fire load	3.41 kWh
-----------	----------

Resistance

Continuity resistor	1 mΩ
---------------------	------

Cable

Cable permanent temperature resistant to	70 °C
--	-------

Sustainability

RoHS conform	Yes
--------------	-----