



4584

**Modular FCC soc. out. 8/8pole, cat.6A, com-tech**

**Technical Features**

**Frequency**

Transmission bandwidth	500 - 500 MHz
------------------------	---------------

**Equipment**

Number of outputs	2
-------------------	---

**Use conditions**

Operating temperature	-40 - 70 °C
-----------------------	-------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Voltage**

Rated voltage	72 V
---------------	------

**Electric current**

Rated current	0.50 A
---------------	--------

**Dimensions**

Built-in depth	35 mm
----------------	-------

**Texts**

Outlet	With straight outlet
Voltage	Suitable for PoE+
Installation mode	Without spreader claws
Category/ports	Cat.6A, Class EA, unshielded
Protection	With optional dust protection hinged covers
Type of connection	With IDC terminals

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes