



4584

Modular FCC soc. out. 8/8pole, cat.6A, com-tech

Technical Features

Frequency

Transmission bandwidth	500 - 500 MHz
------------------------	---------------

Equipment

Number of outputs	2
-------------------	---

Use conditions

Operating temperature	-40 - 70 °C
-----------------------	-------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Voltage

Rated voltage	72 V
---------------	------

Texts

Installation mode	Without spreader claws
Type of connection	With IDC terminals
Voltage	Suitable for PoE+

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes