



WNA402

cubyko Double horizontal flush adapter grey IP55

Technical Features

Capacity

Number of gangs	2
Number of modules	2

Materials

Colour	Light grey
RAL code	7035
Surface finish	Mat
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	154 mm
Width	83 mm
Depth	38 mm
Number of units horizontal	2
Number of units vertical	1

Accessories

Has labelling field	No
---------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting For vertical mounting
-------------------	--

Sustainability

Halogen free	Yes
REACH conform	Yes
RoHS conform	Yes