



WNA403B

cubyko Triple horizontal flush adapter white IP55

Technical Features

Capacity

Number of gangs	3
Number of modules	3

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	224 mm
Width	83 mm
Depth	38 mm

Accessories

Has labelling field	No
---------------------	----

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting For horizontal mounting
-------------------	--

Sustainability

REACH-SVHC free	Yes
-----------------	-----