



4587



FCC soc. out. 8/8pole shielded, cat.6 iso, com-tech

**Technical Features**

**Frequency**

Transmission bandwidth 500 - 500 MHz

**Equipment**

Number of outputs 2

**Use conditions**

Operating temperature -40 - 70 °C

**Connection**

Connector/plug type LSA+ terminal

**Safety**

Ingress Protection (IP) class IP20

**Voltage**

Rated voltage 72 V

**Electric current**

Rated current 1 A

**Dimensions**

Built-in depth 31 mm

**Texts**

Outlet With 45° oblique outlet

Voltage Suitable for PoE+

Installation mode Screw fastening via supporting plate  
Without spreader claws

Protection No

Supporting plate/supporting ring External eyelets on the supporting ring can be broken off for round designs

Type of connection With LSA + terminals

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes