



4588



Modular FCC soc. out. 8/8pole shielded, cat.6 iso, com-tech

Technical Features

Frequency

Transmission bandwidth 500 - 500 MHz

Equipment

Number of outputs 2

Use conditions

Operating temperature -40 - 70 °C

Equipment

With hinged lid No

Materials

Colour Black

Connection

Connector/plug type UAE/IAE (ISDN)

Materials

Material Metal
Plastic

Safety

Ingress Protection (IP) class IP20

Voltage

Rated voltage 72 V

Electric current

Rated current 0.50 A

Dimensions

Built-in depth 35 mm

Texts

Outlet With straight outlet

Voltage Suitable for PoE+

Installation mode For screw fastening
Without spreader claws

Category/ports Cat.6A iso, class EA, shielded

Protection With optional dust protection hinged covers

Supporting plate/supporting ring External eyelets on the supporting ring can be broken off for round designs

Type of connection With IDC terminals

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes