



450210



**Aerial soc. 2hole single box, 1930/glass/R.classic**

**Technical Features**

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Attenuation**

Tap loss at 2150 MHz	5 dB
Tap loss at 860 MHz	4 dB

**Connection**

Connector/plug type	End socket
---------------------	------------

**Frequency**

Frequency bandwidth	5 - 2400 MHz
Broadband technology	5 - 2400 MHz

**Equipment**

Number of outputs	2
-------------------	---

**Materials**

Material	Metal
----------	-------

**Dimensions**

Depth	27.20 mm
Built-in depth	40 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Texts**

Function	Suitable for HDTV
Voltage	Direct voltage conducting (IN / IEC jack female)
Type of connection	With plug-in terminals
Supporting plate/supporting ring	External eyelets on the supporting ring can be broken off for round designs

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes