



HWX002H

Spring charging motor 48-60V AC 50/60Hz HW1 (MO)

Technical Features

Electric current

Rated current	9.60 A
---------------	--------

Voltage

Type voltage supply	AC
Rated insulation voltage U_i	450 V
Rated impulse withstand voltage U_{imp}	6000 V
Command voltage AC	48 - 60 V

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes