



936752568

Ser push-button, 2 NO cont com inp term, Integro - Design Flow/Pure, chr m, lacq

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Double push button
Number of poles	2

Materials

Colour	Chrome
Surface finish	Matt
Material	Thermoplastic
Treatment	Chrome plated Varnished
Transparent	No

Dimensions

Height	55.50 mm
Width	55.50 mm
Depth	24.10 mm
Built-in depth	10 mm
Built-in depth flush-mounted boxes	13 mm

Controls and indicators

Number of buttons	2
Type of push button	Series push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Terminal	Common input terminal
Type of connection	With screw terminals

Sustainability

RoHS conform	Yes
--------------	-----