



WBQP2XS

FIN DGPO 10A with Extra Switch

Technical Features

Electric current

Rated current 10 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Installation, mounting

Mounting on Flush mounting

Mounting-/Connection Position Horizontal

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Australian standard AS/NZS 3112

Rotated central insert No

With hinged lid No

Capacity

Number of modules 2

Safety

Ingress Protection (IP) class IP2X

Functions

With orientation lighting No

Texts

Cover Full cover plate

Type of connection With screw terminals

Suitable for

finesse

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes