



JF408BG

## 400A 16 Way 125A Outgoers Glazed

### Technical Features

#### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 400 A |
|---------------|-------|

#### Equipment

|                            |     |
|----------------------------|-----|
| With lock                  | Yes |
| Has neutral terminal block | Yes |

#### Dimensions

|        |         |
|--------|---------|
| Height | 1550 mm |
| Width  | 900 mm  |
| Depth  | 220 mm  |

#### Cover, door

|                           |     |
|---------------------------|-----|
| Door/cover is transparent | Yes |
|---------------------------|-----|

#### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

#### Safety

|                               |                         |
|-------------------------------|-------------------------|
| Protection class              | Isolation class III     |
| Impact resistance IK          | IK05                    |
| Ingress Protection (IP) class | IP30                    |
| Locking type                  | Barrel lock<br>Key lock |

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|