



936752518



Ser p-b, 2 NO cont com inp term, Integro - Design Flow/Pure, chr gl, galv

#### Technical Features

##### Electric current

Momentary contact current	10 A
---------------------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Architecture

Control/operation element	Double push button
---------------------------	--------------------

Number of poles	2
-----------------	---

##### Materials

Colour	Chrome
--------	--------

Surface finish	Glossy
----------------	--------

Material	Thermoplastic
----------	---------------

Treatment	Chrome plated Coated
-----------	-------------------------

Transparent	No
-------------	----

##### Dimensions

Height	55.50 mm
--------	----------

Width	55.50 mm
-------	----------

Depth	25 mm
-------	-------

Built-in depth	10 mm
----------------	-------

Built-in depth flush-mounted boxes	13 mm
------------------------------------	-------

##### Controls and indicators

Number of buttons	2
-------------------	---

Type of push button	Series push button
---------------------	--------------------

With feedback signal contact	No
------------------------------	----

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Impact resistance IK	IK05
----------------------	------

##### Accessories

Has labelling field	No
---------------------	----

##### Texts

Imprint	Without imprint
---------	-----------------

Lighting	Without lighting (cannot be illuminated)
----------	--

Terminal	Common input terminal
----------	-----------------------

Type of connection	With screw terminals
--------------------	----------------------

##### Sustainability

RoHS conform	Yes
--------------	-----