



VSR114

### Design 50 Consumer Unit, 14 Way, 100A Switch Disconnect Incomer

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Architecture

Number of poles	2
-----------------	---

##### Functions

Overvoltage protection	No
------------------------	----

##### Capacity

Number of modules	14
-------------------	----

##### Electric current

Rated current	100 A
---------------	-------

##### Dimensions

Depth	105 mm
Height	284 mm
Width	431 mm
Thickness of sidewall	1 mm

##### Cover, door

Interlockable	No
Door/cover is transparent	No

##### Materials

RAL code	9010
Colour	Pure white
Material	Steel

##### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

##### Connection

Number of accessible phases	1
-----------------------------	---

##### Equipment

Number of rows	1
Number of rails	1
Extension possible	No

##### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC
Protection class	Isolation class I

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes