



VP20M

Enclosure, Vector, Polycarbonate, plain door, IP65, 2x10M, 350x250x160 mm

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	2
-----------------	---

Number of rows	2
----------------	---

Number of section in width	1
----------------------------	---

With lock	Yes
-----------	-----

Has neutral terminal block	No
----------------------------	----

Capacity

Number of modules	20
-------------------	----

Dimensions

Height	350 mm
--------	--------

Width	250 mm
-------	--------

Depth	160 mm
-------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	160 mm
----------------	--------

Number of width units	10
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Materials

Material	Plastic
----------	---------

RAL code	7035
----------	------

Colour	Light grey
--------	------------

Equipment

Has earthing terminal block	No
-----------------------------	----

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class II
------------------	--------------------

Ingress Protection (IP) class	IP65
-------------------------------	------

Locking type	3-Side 7 mm
--------------	-------------

Glow wire test	850 °C
----------------	--------

Sustainability

RoHS conform	Yes
--------------	-----