



VP20M

Enclosure, Vector, Polycarbonate, plain door, IP65, 2x10M, 350x250x160 mm

Technical Features

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 2

Number of rows 2

Number of section in width 1

With lock Yes

Has neutral terminal block No

Capacity

Number of modules 20

Dimensions

Height 350 mm

Width 250 mm

Depth 160 mm

Cover, door

Number of cabinet doors 1

Dimensions

Built-in depth 160 mm

Number of width units 10

Cover, door

Door/cover is transparent Yes

Materials

Material Plastic

RAL code 7035

Colour Light grey

Equipment

Has earthing terminal block No

Has mounting plate No

Safety

Protection class Isolation class II

Ingress Protection (IP) class IP65

Locking type 3-Side 7 mm

Glow wire test 850 °C

Sustainability

RoHS conform Yes