



SU213

**Bell 220/240V**

**Technical Features**

**Electric current**

Rated current	0.03 A
---------------	--------

**Dimensions**

Dimensions	81 x 18 mm
Height	81 mm
Width	18 mm
Depth	64 mm

**Use conditions**

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

**Connection**

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

**Power**

Total power loss under I <sub>N</sub>	6.50 W
Power consumption VA	6.50 VA

**Equipment**

Noise level	85
-------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Capacity**

Number of modules	1
-------------------	---

**Voltage**

Rated operational voltage U <sub>e</sub>	220 - 240 V
--	-------------

**Illustrations | Drawings**

