



SU213

Bell 220/240V

Technical Features

Electric current

Rated current	0.03 A
---------------	--------

Dimensions

Dimensions	81 x 18 mm
Height	81 mm
Width	18 mm
Depth	64 mm

Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Power

Total power loss under IN	6.50 W
Power consumption VA	6.50 VA

Equipment

Noise level	85
-------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U _e	220 - 240 V
--	-------------

Illustrations | Drawings

