



WBHP1S

### Allure Single GPO 10A

#### Technical Features

##### Electric current

Rated current	10 A
---------------	------

##### Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC) Thermoplastic
Treatment	Untreated

##### Dimensions

Height	82 mm
Width	120 mm
Depth	9.50 mm
Number of units	1
Built-in depth flush-mounted boxes	18 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK08
Ingress Protection (IP) class	IP2X

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Without enhanced contact protection
Type of connection	With screw terminals

##### Suitable for

allure

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes