



WNA685B

**IP55**

**cubyko Double horizontal box empty with 4 sliders white IP55**

**Technical Features**

**Capacity**

Number of modules	2
-------------------	---

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Contains recycled material (% of total plastic weight)	0 %
Treatment	Untreated

**Dimensions**

Number of units	2
Height	76 mm
Width	147 mm
Depth	56 mm
Built-in depth	65 mm

**Equipment**

With cable entry	Yes
------------------	-----

**Installation, mounting**

Mounting-/Connection Position	Horizontal
Mounting on	Surface mounting

**Accessories**

With frame cover	Yes
------------------	-----

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Safety**

Usable in higher IP class	IP55 with closed cover
---------------------------	------------------------

**Texts**

Installation mode	For horizontal mounting
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

**Suitable for**

cubyko	
cubyko	

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----