



WNA686

cubyko Double vertical box empty grey IP55

Technical Features

Capacity

Number of modules	2
-------------------	---

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Varnished

Dimensions

Number of units	1
Height	147 mm
Width	76 mm
Depth	56 mm

Equipment

With cable entry	Yes
------------------	-----

Installation, mounting

Mounting-/Connection Position	Vertical
Mounting on	Surface mounting

Accessories

With frame cover	Yes
------------------	-----

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK07

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	For vertical mounting
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Suitable for

Hager cubyko	
cubyko	

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes