



11376086

Centre plate f.rot. dimmer/potentiometer, setting knob, Q.x, ant.velv.lacq.

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Anthracite
RAL code	7016
Surface finish	Velvety
Material	Duroplastic
Treatment	Varnished

Dimensions

Height	58.50 mm
Width	58.50 mm
Depth	17.50 mm
Diameter axis	4 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Imprint	Centre plate without imprint
Installation mode	For screw fastening

Suitable for

Berker Q.x	
------------	--

Sustainability

Halogen free	Yes
REACH conform	Yes
RoHS conform	Yes