



11376089

Centre plate f. rot. dimmer/potentiometer, setting knob,Q.x,p.white velv.

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Duroplastic
Treatment	Untreated

Dimensions

Height	58.50 mm
Width	58.50 mm
Depth	17.50 mm
Diameter axis	4 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
Usable in higher IP class	IP44 in combination with sealing set

Texts

Imprint	Centre plate without imprint
Installation mode	For screw fastening

Suitable for

Q.x	
-----	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes