



11376089

**Centre plate f. rot. dimmer/potentiometer, setting knob,Q.x,p.white velv.**

**Technical Features**

**Architecture**

Control/operation element	Rotative
---------------------------	----------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Duroplastic
Treatment	Untreated

**Dimensions**

Height	58.50 mm
Width	58.50 mm
Depth	17.50 mm
Diameter axis	4 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP20
Usable in higher IP class	IP44 in combination with sealing set

**Texts**

Imprint	Centre plate without imprint
Installation mode	For screw fastening

**Suitable for**

Q.x	
-----	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes