



11376084

Technical Features

Architecture

| | |
|---------------------------|------------------------|
| Control/operation element | Push & rotative switch |
|---------------------------|------------------------|

Materials

| | |
|----------------|-------------|
| Colour | Aluminium |
| RAL code | 9006 |
| Surface finish | Velvety |
| Material | Duroplastic |
| Treatment | Varnished |

Dimensions

| | |
|---------------|----------|
| Height | 58.50 mm |
| Width | 58.50 mm |
| Depth | 17.50 mm |
| Diameter axis | 4 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Clamp mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|-------------------|------------------------------|
| Imprint | Centre plate without imprint |
| Installation mode | For screw fastening |

Suitable for

| | |
|------------|--|
| Berker Q.x | |
|------------|--|

Sustainability

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |