



6768803512

Soc.out. insert earth.pin+hinged cover surf./flushmtd,enhncd contact prot.,W1,wh

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white
RAL code 9010
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Dimensions

Height 71 mm
Width 71 mm
Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Flush mounting
Surface mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid Yes
With round protective earth pin Yes
With signal lamp No
With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 1

Safety

With enhanced contact protection No
Impact resistance IK IK05
Ingress Protection (IP) class IP55

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

Sustainability

Halogen free	Yes
RoHS conform	Yes