



WNA686B

IP55

**cubyko Double vertical box empty white IP55**

**Technical Features**

**Capacity**

Number of modules

2

**Materials**

Colour

Polar white

RAL code

9010

Surface finish

Matt

Material

Thermoplastic

Treatment

Untreated

**Dimensions**

Number of units

2

Height

147 mm

Width

76 mm

Depth

56 mm

**Equipment**

With cable entry

Yes

**Installation, mounting**

Mounting-/Connection Position

Vertical

Mounting on

Surface mounting

**Accessories**

With frame cover

Yes

**Safety**

Ingress Protection (IP) class

IP55

Impact resistance IK

IK05

**Use conditions**

Operating temperature

-15 - 30 °C

**Texts**

Installation mode

For vertical mounting

Sealing

With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

**Suitable for**

cubyko

cubyko

**Sustainability**

Halogen free

Yes

REACH-SVHC free

Yes

RoHS conform

Yes