



WGCCCH5

**5G multi-gang frame (horizontal)**

**Technical Features**

**Capacity**

Number of gangs	5
Number of modules	0

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Contains recycled material (% of total plastic weight)	0 %
Treatment	Untreated

**Dimensions**

Height	8 mm
Width	86 mm
Depth	8 mm
Number of units horizontal	5
Number of units vertical	5

**Accessories**

Has labelling field	No
---------------------	----

**Installation, mounting**

Mounting on	Mounting plate
-------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Use conditions**

Operating temperature	-20-45 °C
-----------------------	-----------

**Sustainability**

RoHS conform	Yes
--------------	-----