



29521404



LED signal light, red/green lighting, B.7, al., matt, lacq.

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 0.50 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Aluminium
RAL code 9006
Surface finish Matt
Material Metal
Plastic
Treatment Varnished

Dimensions

Height 70 mm
Width 70 mm
Depth 50 mm

Connection

Conductor cross-section 2.50 - 2.50 mm²

Safety

Ingress Protection (IP) class IP20

Texts

Labelling Foil bi-colour with imprinted symbols for Do not disturb / Make up room and Enter/ Wait are supplied
Imprint Without imprint

Suitable for

S.x/B.x

Sustainability

REACH-SVHC free Yes
RoHS conform Yes