



VSR_SIZE_5

12 Way 100A Switch Type 2 SPD

Technical Features

Installation, mounting

Mounting on Flush mounting

Architecture

Number of poles 2

Functions

Overvoltage protection No

Installation, mounting

Suitable for outdoor usage No

Capacity

Number of modules 12

Electric current

Rated current 100 A

Dimensions

Depth 105 mm

Height 284 mm

Width 431 mm

Thickness of sidewall 1 mm

Cover, door

Interlockable No

Door/cover is transparent No

Materials

RAL code 9010

Colour Pure white

Material Steel

Connection

Number of accessible phases 1

Equipment

Number of rows 1

Number of rails 1

Extension possible No

Safety

Impact resistance IK IK05

Ingress Protection (IP) class IP2XC