



TXA210AN

Dimmer 1 channel 300W

Technical Features

Voltage

System supply voltage	30 V DC Via bus
-----------------------	-----------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
----------------------------------	----------------------------

Cross-section rigid conductor	0.75 - 2.5 mm ²
-------------------------------	----------------------------

Equipment

Number of outputs	1
-------------------	---

Type of dimmer	Universal
----------------	-----------

Capacity

Number of modules	4
-------------------	---

Power

Power incandescent lamp	20 - 300 W
-------------------------	------------

Power of variator	0 - 300 W
-------------------	-----------

Connectivity

Type of connection	quickconnect
--------------------	--------------

Settings

Supported configuration mode	ETS easy
------------------------------	-------------