



395619

Pullcord push-button, change-over contact sep. signal contact, light control

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Pull cord
---------------------------	-----------

Materials

Surface finish	Matt
Material	Metal Plastic
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth	31.20 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
Type of push button	Single push button
With feedback signal contact	Yes

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Texts

Imprint	Without imprint
Installation mode	With spreader claws For wall and ceiling mounting
Lighting	For lighting and monitoring circuit
Switch mode	Change-over contact, with separate signal contact
Type of connection	With plug-in terminals

Suitable for

K.x / Q.x / R.x / S.x/B.x

Sustainability

Halogen free	Yes
RoHS conform	Yes