



395619



Pullcord push-button, change-over contact sep. signal contact, light control

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Pull cord
---------------------------	-----------

Materials

Surface finish	Matt
Material	Metal Plastic
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth	31.20 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
Type of push button	Single push button
With feedback signal contact	Yes

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
Installation mode	With spreader claws For wall and ceiling mounting
Lighting	For lighting and monitoring circuit
Switch mode	Change-over contact, with separate signal contact
Type of connection	With plug-in terminals

Suitable for

K.x / Q.x / R.x / S.x/B.x

Sustainability

Halogen free	Yes
RoHS conform	Yes