



WBWP115S

**Socket IP53 single horizontal 15A**

**Technical Features**

**Electric current**

|               |      |
|---------------|------|
| Rated current | 15 A |
|---------------|------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

**Materials**

|                |                        |
|----------------|------------------------|
| Colour         | Light grey             |
| Surface finish | Glossy                 |
| Material       | Glass<br>Thermoplastic |
| Treatment      | Untreated              |

**Dimensions**

|        |       |
|--------|-------|
| Height | 85 mm |
| Width  | 85 mm |
| Depth  | 88 mm |

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type      | Screw mounting |

**Equipment**

|                                   |                                 |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert            | No                              |
| With hinged lid                   | No                              |
| With round protective earth pin   | No                              |
| With signal lamp                  | No                              |

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Safety**

|                               |      |
|-------------------------------|------|
| Impact resistance IK          | IK08 |
| Ingress Protection (IP) class | IP53 |

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

**Texts**

|                    |                                     |
|--------------------|-------------------------------------|
| Cover              | Complete housing                    |
| Protection         | Without enhanced contact protection |
| Type of connection | With screw terminals                |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |